



- ★ : Require proper type of adhesive.
- ★a : Two-component adhesive (Epoxy resin system)
- ★b : Instant adhesive
- ★c : Thread locking adhesives (Anaerobic adhesive)
- ※ : Grease (Grease that doesn't affect plastic)

No.	PART No.	DISCRIPTION	Q'TY USED	NOTE
1	JB30-1	JB-30 Base		
2	JB30-2	Head mount platform cushion rubber	1	
3	JB30-3	Φ75mm Adaptor	1	
4	JB30-4	Ball cup	1	
5	JB30-5	Ball cup lock knob	1	2 Pcs. set
6	JB30-6	Head mount platform spacer	1	
7	JB30-7	Level (Tilt)	1	
8	JB30-8	Hexagon socket screw key holder	1	
9	JB30-9	Hexagon socket screw key	1	
10	JB30-10	Boom friction knob	1	
11	JB30-11	Pipe shaft	2	
12	JB30-12	Level (Pan)	1	
13	JB30-13	Pan friction knob	2	
14	JB30-14	Cushion rubber	1	
15	JB30-15	Main arm lock screw	1	2 Pcs. set
16	JB30-16	Counter arm lock screw	1	
17	JB30-17	Weight bushing	1	
18	JB30-18	Weight fixing nut	2	
19	JB30-19	Weight shaft screw	1	
20	JB30-20	Inner support arm	1	
21	JB30-21	Support arm rubber	1	2 Pcs. set
22	JB30-22	Outer support arm	1	
23	JB30-23	Adjusting lock lever	1	
24	JB30-24	Fixing handle	1	
25	JB30-25	JB-30 Holding band	1	
26	JB30-26	Adjusting weight	1	
27	JB30-27	Pan handle fixing base	2	
28	JB30-28	Safety lock assembly	1	